



Sample image

**Order symbol:** D-MP

**Product nbr:** 8524062

**Description:** Back Panel. for enclosures:

**Remarks:** 170x80x65. 170x80x85

**Including:**

**EAN:** 6418074033598

**El. number:**

- Finland: 3423908
- Denmark: 8212002131
- Sweden: 2536934

**Dimensions:**

	Length	Width	Height
mm:		54	140
inch:		2.13	5.51

**Materials:**

Material: \_\_\_\_\_

Base colour: \_\_\_\_\_

Cover colour: \_\_\_\_\_

Gasket material: \_\_\_\_\_

**Temperatures:**

Temperature °C (short term): \_\_\_\_\_

Temperature °C (continuous): \_\_\_\_\_

Temperature °F (short term): \_\_\_\_\_

Temperature °F (continuous): \_\_\_\_\_

**Rating:**

Ingress protection (EN 60529): \_\_\_\_\_

Impact Resistance (EN 62262): \_\_\_\_\_

Electrical insulation: \_\_\_\_\_ Not insulated

Halogen free (DIN/VDE 0472, Part 815): \_\_\_\_\_ 0

UV resistance: \_\_\_\_\_ -

Flammability Rating: \_\_\_\_\_

Glow Wire Test (IEC 695-2-1) °C: \_\_\_\_\_

NEMA Class \_\_\_\_\_

**Certificates:** \_\_\_\_\_