

DRS ARCA 403015

FIBOX
Enclosing innovations



Sample image

Order symbol: DRS ARCA 403015

EAN: 6418074082855

Product nbr: 8120764


El. number:

Description: DIN rail frame set

- Finland: 3423856
- Denmark: 8212094709
- Sweden: 2500190

Remarks: 2 rows x 11 modules. for size 400x300x150

Including:



Dimensions:	Length	Width	Height
-------------	--------	-------	--------

mm:		285	385
-----	--	-----	-----

inch:		11.22	15.16
-------	--	-------	-------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates: