

DEDS0200

IP66, IK10 Lockable solid door steel enclosure 350x250x150 with galvanised wall mounting brackets. Power coated galvanised Grey (RAL 7035) steel housing and galvanised back plate guaranteed for 3 years against corrosion.



SPECIFICATION

Product Type	Solid door enclosures
Door Style	Solid
Enclosure Material	Steel
Door Material	Steel
IP Rating	66
Colour	Grey (RAL 7035)
Min Temperature °C	-20
Max Temperature °C	55
Size (mm)	350x250x150
Height (mm)	350
Width (mm)	250
Depth (mm)	150
Gland Plate (mm)	168x95
Mounting Plate (mm)	315x200
Number of Locks	1
Comments	Lockable, with galvanized steel back plate and wall mounting brackets supplied
Accessories Available	Kwik fix cable gland

DISTRIBUTORS

