

**MNX ABS 95/60 HG**



Sample photo

**Order symbol:** ABS 95/60 HG  
**Product nbr:** 6081331  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074054715  
**EI. number:**  
 Finland: 3421380  
 Electric No. 8212023987  
 Denmark:  
 Electric No. Sweden: 6081331

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	100	100	60	MIN 8 DIN-15 Mounting rail
inch:	3.9	3.9	2.4	B-3 DIN-35 Mounting rail
				FP 22046 Wall fastening lug (4 pcs)

Materials:	Rating:
<b>Material:</b> ABS	Ingress Protection (EN 60529): IP66/IP67
<b>Base colour:</b> RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
<b>Cover screws material:</b> Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b> RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b> Grey	Flammability Rating: UL 94 HB
<b>Gasket material:</b> Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
	NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	Certificates:
<b>Temperature °C (short term):</b> -40 ... 80 °C	SGS Fimko
<b>Temperature °C (continuous):</b> -40 ... 60 °C	Gost R
<b>Temperature °F (short term):</b> -40 ... 175 °F	
<b>Temperature °F (continuous):</b> -40 ... 140 °F	

Accessories:
MIV 95                      Mounting plate (Galvanized steel)

