

PC 125/35 LG

FIBOX


Enclosing innovations



Sample image

Order symbol: PC 125/35 LG**Product nbr:** 6012307**UL Code:** 6412307**UL Name:** UL PC 125/35 LG**Description:** Enclosure. PC**Remarks:** Opaque cover**Including:** Base with TPE gasket. screws for mounting plate/DIN-rail and cover with polyamide cover screws.**EAN:** 6418074022073**El. number:**

- Finland: 3420323
- Denmark: 8212022069
- Sweden: 2535521



Dimensions:	Height	Width	Depth
mm:	130	130	35
inch:	5.12	5.12	1.38

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

MIV 10	DIN-35 Mounting rail. for enclosures: (100 x 35 x 1)
HFP 130	Front panel hinge series for FP A 100-125
FP A 125/130	Front panel (Aluminum). for enclosures: (120 x 112 x 1)
MIN 10	DIN-15 Mounting rail. for enclosures: (100 x 15 x 1)
FP 22046	Mounting foot kit (4 pcs)
MIV 125	Back Panel (Galvanized steel). for enclosures: (98 x 98 x 1)

Rating:

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

Certificates:

Certificate FI 40847