

Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	560	280	130
-----	-----	-----	-----

inch:			
-------	--	--	--

Materials:

Material:	Polycarbonate
-----------	---------------

Base colour:	RAL 7035 -light grey
--------------	----------------------

Cover colour:	RAL 7035 -light grey
---------------	----------------------

Gasket material:	Polyurethane
------------------	--------------

Temperatures:

Temperature °C (short term):	-40 ... 120
------------------------------	-------------

Temperature °C (continuous):	-40 ... 80
------------------------------	------------

Temperature °F (short term):	-40 ... 250
------------------------------	-------------

Temperature °F (continuous):	-40 ... 175
------------------------------	-------------

Accessories:

EKTZR	Extension frame. for enclosures: (560 x 280 x 50)
-------	--

EKTVT	Back Panel. for enclosures: (518 x 238 x 1)
-------	--

EKV 22	DIN-35 Mounting rail. for enclosures: (235 x 35 x 1)
--------	---

EKV 50	DIN-35 Mounting rail. for enclosures: (515 x 35 x 1)
--------	---

Rating:

Ingress protection (EN 60529):	IP66; IP67;
--------------------------------	-------------

Impact Resistance (EN 62262):	IK08;
-------------------------------	-------

Electrical insulation:	Totally insulated
------------------------	-------------------

Halogen free (DIN/VDE 0472, Part 815):	1
--	---

UV resistance:	UL 508
----------------	--------

Flammability Rating:	UL 746C 5*
----------------------	------------

Glow Wire Test (IEC 695-2-1) °C:	960 °C
----------------------------------	--------

NEMA Class	
------------	--

Certificates:

Certificate NCS FI 30308
