

## Features:

Light grey polycarbonate box, 115 x 65 x 55mm with tongue-and-groove sealing system plus neoprene gasket giving sealing to **IP65**.

- Wall mounting holes and lid fixing screws are outside the sealed area preventing ingress of dust and moisture
- Internal guide slots for mounting PCBs vertically
- Bosses with threaded brass inserts in base for horizontal mounting of PCBs or terminals
- Non-magnetic M4 lid fixing screws
- Temperature range  $-40$  to  $+125^{\circ}\text{C}$

