



Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	255	180	125
-----	-----	-----	-----

inch:			
-------	--	--	--

Materials:	
------------	--

Material:	Polycarbonate
-----------	---------------

Base colour:	RAL 7035 -light grey
--------------	----------------------

Cover colour:	Clear transparent
---------------	-------------------

Gasket material:	Polyurethane
------------------	--------------

Temperatures:	
---------------	--

Temperature °C (short term):	-40 ... 120
------------------------------	-------------

Temperature °C (continuous):	-40 ... 80
------------------------------	------------

Temperature °F (short term):	-40 ... 250
------------------------------	-------------

Temperature °F (continuous):	-40 ... 175
------------------------------	-------------

Accessories:	
--------------	--

MIN 20	DIN-15 Mounting rail. for enclosures: (225 x 15 x 1)
--------	---

HFP 180	Front panel hinge series
---------	--------------------------

MIN 15	DIN-15 Mounting rail. for enclosures: (150 x 15 x 1)
--------	---

MIV 200	Back Panel (Galvanized steel). for enclosures: (223 x 148 x 1)
---------	---

FP A 200/180	Front panel (Aluminum). for enclosures: (237 x 170 x 1)
--------------	--

MIV 15	DIN-35 Mounting rail. for enclosures: (150 x 35 x 1)
--------	---

FP 22046	Mounting foot kit (4 pcs)
----------	---------------------------

MIV 20	DIN-35 Mounting rail. for enclosures: (225 x 35 x 1)
--------	---

Rating:	
---------	--

Ingress protection (EN 60529):	IP66; IP67;
--------------------------------	-------------

Impact Resistance (EN 62262):	IK08;
-------------------------------	-------

Electrical insulation:	Totally insulated
------------------------	-------------------

Halogen free (DIN/VDE 0472, Part 815):	1
--	---

UV resistance:	UL 508
----------------	--------

Flammability Rating:	UL 746C 5*
----------------------	------------

Glow Wire Test (IEC 695-2-1) °C:	960 °C
----------------------------------	--------

NEMA Class	
------------	--

Certificates:	
---------------	--

Certificate FI 40847	
----------------------	--