

PCT 081206

FIBOX
Enclosing innovations



Sample image

Order symbol: PCT 081206

Product nbr: 7022581

UL Code: 70325B1

UL Name: UL PCT 081206

Description: Enclosure. PC


Remarks: Clear transparent cover

Including: Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.

EAN: 6418074003744

El. number:

- Finland: 3423528
- Denmark: 8212002636
- Sweden:



Dimensions:	Height	Width	Depth
mm:	80	120	55
inch:	3.15	4.72	2.17

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Clear transparent
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

TRM 0812	DIN-15 Mounting rail. for enclosures: (106 x 15 x 1)
TF 28037	Mounting foot kit (4 pcs). for enclosures:
TM 0812	Back Panel. for enclosures: (71 x 94 x 1)
ARH 12	DIN-35 Mounting rail. for enclosures: (105 x 35 x 1)
TH A	Gray plastic hinges (2 pcs)
TRM 0808	DIN-15 Mounting rail. for enclosures: (68 x 15 x 1)

Rating:

Ingress protection (EN 60529):	IP66; IP67;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 746C 5*
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

Certificates:

SGSFimko_EURONORD