

# TM 1534



Sample image

**Order symbol:** TM 1534

**Product nbr:** 9512021

**Description:** Back Panel. for enclosures:

**Remarks:** 340x150x101.  
340x150x121

**Including:**

**EAN:** 6418074059437

**El. number:**

- Finland: 3420812
- Denmark: 8212003994
- Sweden: 2536164

Dimensions:	Length	Width	Height
mm:		136	303
inch:		5.35	11.93

#### Materials:

Material:

Base colour:

Cover colour:

Gasket material:

#### Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

#### Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

#### Certificates: