

TM 1636



Sample image

Order symbol: TM 1636

Product nbr: 9512023

Description: Back Panel, for enclosures:

Remarks: 360x160x101

Including:

EAN: 6418074059444

El. number:

- Finland: 3420816
- Denmark: 8212004032
- Sweden: 2536167

Dimensions:	Height	Width	Depth
-------------	--------	-------	-------

mm:	318	146	1
-----	-----	-----	---

inch:	12.52	5.75	0.04
-------	-------	------	------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation:	Not insulated
------------------------	---------------

Halogen free (DIN/VDE 0472, Part 815):	0
--	---

UV resistance:	-
----------------	---

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:	C
----------------------------------	---

NEMA Class

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Certificates: