

TM 2330



Sample image

Order symbol: TM 2330

Product nbr: 9512019

Description: Back Panel. for enclosures:

Remarks: 300x230x87.
300x230x110

Including:

EAN: 6418074034083

El. number:

- Finland: 3423929
- Denmark: 8212004074
- Sweden: 2536169

Dimensions:	Length	Width	Height
mm:		274	221
inch:		10.79	8.7

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Certificates: