



Order symbol: TPC 090706
Product nbr: 5824038
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074309556
EI. number:
Finland:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions: Length Width Height Accessories:

mm:	95	65	60
inch:	3.7	2.6	2.4

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Rating:

Ingress Protection (EN 60529): IP65
 Impact Resistance (EN 62262): IK07/IK08
 Electrical insulation: Totally insulated
 Halogen free (DIN/VDE 0472, Part 815): 1
 Flammability Rating: UL 746C 5"
 Glow Wire Test (IEC 695-2-1) °C: 960
 NEMA Class: NEMA 1, 4, 4X, 12

Certificates:

SGS Fimko

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

FP 10674

