

TEMPO TPC 131308



Order symbol: TPC 131308
Product nbr: 5824041
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074049773
EI. number:
Finland:

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	130	130	75	Rating: Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07/IK08 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 Flammability Rating: UL 746C 5" Glow Wire Test (IEC 695-2-1) °C: 960 NEMA Class: NEMA 1, 4, 4X, 12
inch:	5.1	5.1	3.0	

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:
FP 10674

