

TPC 241911T



Sample image

Order symbol: TPC 241911T

Product nbr: 5824007

Description: Enclosure. PC



Remarks: Clear transparent cover

EAN: 6418074086778

Including:

El. number:

- Finland:
- Denmark:
- Sweden:



Dimensions:

	Height	Width	Depth
mm:	240	191	107
inch:	9.45	7.52	4.21

Materials:

Material: Polycarbonate

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):: -40 ... 120

Temperature °C (continuous):

Temperature °F (short term): -40 ... 250

Temperature °F (continuous): -40 ... 175

Accessories:

MP 2419	Mounting plate. for enclosures: (210 x 160 x 0)
EKV 12	DIN-35 Mounting rail. for enclosures: (160 x 35 x 1)
DR 210	DIN-35 Mounting rail. for enclosures: (210 x 35 x 1)
FP 10674	Mounting foot kit (2 pcs) incl. screws

Rating:

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07; IK08;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	-
Flammability Rating:	UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	

Certificates:

Certificate FI 40343