



**Order symbol:** TPC 292411T  
**Product nbr:** 5824008  
**Description:** Enclosure, PC  
**Remarks:** Clear transparent cover

**EAN:** 6418074086839  
**EI. number:**  
**Finland:**

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	289	239	107	DR 265 DIN-35 Mounting rail
inch:	11.4	9.4	4.2	DR 215 DIN-35 Mounting rail FP 10674

Materials:	Rating:
<b>Material:</b> Polycarbonate	Ingress Protection (EN 60529): IP65
<b>Base colour:</b> RAL 7035 -light grey	Impact Resistance (EN 62262): IK07/IK08
<b>Cover screws material:</b> Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b> RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b> Grey	Flammability Rating: UL 746C 5"
<b>Gasket material:</b> Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 960
	NEMA Class: NEMA 1, 4, 4X, 12

Temperatures:	Certificates:
<b>Temperature °C (short term):</b> -40 ... 120 °C	SGS Fimko
<b>Temperature °C (continuous):</b> -40 ... 80 °C	
<b>Temperature °F (short term):</b> -40 ... 250 °F	
<b>Temperature °F (continuous):</b> -40 ... 175 °F	

Accessories:
MP 2924                      Mounting plate

