

CARDMASTER ABS 17/16-LC3



Sample photo

Order symbol: ABS 17/16-LC3
Product nbr: 7580104
Description: Enclosure, ABS
Remarks: Without main cover

EAN: 6418074039316
El. number:
 Finland: 3421780
 Electric No. 8212016732
 Denmark:
 Electric No. Sweden: 7580104

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	166	160	80	FP 17/16 Front plate (aluminium)
inch:	6.5	6.3	3.1	FC PC 17/16 Frame of PC front plate
Materials:				Rating:
Material:	ABS			Ingress Protection (EN 60529): IP65
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07
Gasket material:	EPDM			Electrical insulation: Totally insulated
Temperatures:				Halogen free (DIN/VDE 0472, Part 815): 1
Temperature °C (short term):	-40 ... 80 °C			Flammability Rating: UL 94 HB
Temperature °C (continuous):	-40 ... 60 °C			Glow Wire Test (IEC 695-2-1) °C: 650
Temperature °F (short term):	-40 ... 175 °F			NEMA Class: NEMA 1, 3, 3R, 12, 13
Temperature °F (continuous):	-40 ... 140 °F			Certificates:
Accessories:				Gost R
MP 17/16	Mounting plate			

