

**CARDMASTER PC 17/16-3**



Sample photo

**Order symbol:** PC 17/16-3  
**Product nbr:** 7525165  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent hinged cover

**EAN:** 6418074056726  
**EI. number:**  
 Finland: 3438230  
 Electric No. 8212016648  
 Denmark:  
 Electric No. Sweden: 2537302

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	166	160	134	FP 17/16	Front plate (aluminium)
inch:	6.5	6.3	5.3	FC PC 17/16	Frame of PC front plate
Materials:				Rating:	
<b>Material:</b>	Polycarbonate			Ingress Protection (EN 60529): IP65	
<b>Base colour:</b>	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08	
<b>Cover colour:</b>	Smoked grey			Electrical insulation: Totally insulated	
<b>Gasket material:</b>	EPDM & PUR			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperatures:</b>				UV resistance: UL 508	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Flammability Rating: UL 746C 5V	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			NEMA Class: NEMA 1, 3, 3R, 4, 4X, 12, 13	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			<b>Certificates:</b>	
<b>Accessories:</b>				SGS Fimko	
MP 17/16	Mounting plate			Gost R	

