

CARDMASTER PC 21/18-3



Order symbol: PC 21/18-3
Product nbr: 7525154
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056733
EI. number:
 Finland: 3438231
 Electric No. 8212016664
 Denmark:
 Electric No. Sweden: 2537306

Including: Base, terminal compartment cover with PUR gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Accessories:		
mm:		235	185	119	FP 21/18	Front plate (aluminium)	
inch:		9.3	7.3	4.7	FC PC 21/18	Frame of PC front plate	
Materials:						Rating:	
Material:		Polycarbonate			Ingress Protection (EN 60529): IP65		
Base colour:		RAL 7035 -light grey			Impact Resistance (EN 62262): IK07/IK08		
Cover colour:		Smoked grey			Electrical insulation: Totally insulated		
Gasket material:		EPDM & PUR			Halogen free (DIN/VDE 0472, Part 815): 1		
Temperatures:						UV resistance: UL 508	
Temperature °C (short term):		-40 ... 120 °C			Flammability Rating: UL 746C 5V		
Temperature °C (continuous):		-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 960		
Temperature °F (short term):		-40 ... 250 °F			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13		
Temperature °F (continuous):		-40 ... 175 °F			Certificates:		
Accessories:						SGS Fimko	
MP 21/18		Mounting plate			Gost R		

