



**Order symbol:** PC 25/22-3  
**Product nbr:** 7525134  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent hinged cover

**EAN:** 6418074059390  
**EI. number:**  
**Finland:** 3438232  
**Electric No. Sweden:** 7525134

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	280	219	156	FP 25/22 Front plate (aluminium)
inch:	11.0	8.6	6.1	FC PC 25/22 Frame of PC front plate
Materials:	Material: Polycarbonate			Rating:
Base colour:	RAL 7035 -light grey			Ingress Protection (EN 60529): IP65
Cover colour:	Smoked grey			Impact Resistance (EN 62262): IK07/IK08
Gasket material:	EPDM & PUR			Electrical insulation: Totally insulated
Temperatures:	Temperature °C (short term): -40 ... 120 °C			Halogen free (DIN/VDE 0472, Part 815): 1
Temperature °C (continuous):	-40 ... 80 °C			UV resistance: UL 508
Temperature °F (short term):	-40 ... 250 °F			Flammability Rating: UL 746C 5V
Temperature °F (continuous):	-40 ... 175 °F			Glow Wire Test (IEC 695-2-1) °C: 960
Accessories:	MP 25/22 Mounting plate			NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
				Certificates:
				SGS Fimko
				Gost R

