

**CARDMASTER PC 25/22-FC3**



**Order symbol:** PC 25/22-FC3  
**Product nbr:** 7520241  
**Description:** Enclosure, PC  
**Remarks:** Grey screw cover

**EAN:** 6418074059376  
**El. number:**  
**Finland:** 3438227  
**Electric No. Sweden:** 7520241

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	257	219	135	FP 25/22 Front plate (aluminium)
inch:	10.1	8.6	5.3	FC PC 25/22 Frame of PC front plate
Materials:	Material: Polycarbonate			Rating:
	Base colour: RAL 7035 -light grey			Ingress Protection (EN 60529): IP65
	Gasket material: EPDM & PUR			Impact Resistance (EN 62262): IK07/IK08
Temperatures:	Temperature °C (short term): -40 ... 120 °C			Electrical insulation: Totally insulated
	Temperature °C (continuous): -40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1
	Temperature °F (short term): -40 ... 250 °F			UV resistance: UL 508
	Temperature °F (continuous): -40 ... 175 °F			Flammability Rating: UL 746C 5V
Accessories:	MP 25/22 Mounting plate			Glow Wire Test (IEC 695-2-1) °C: 960
				NEMA Class: NEMA 1, 3, 3R, 4X, 12, 13
				Certificates:
				SGS Fimko
				Gost R

