

**ARCA 504021**

**Order symbol:** ARCA 504021  
**Product nbr:** 8120011  
**Description:** Cabinet, PC  
**Remarks:** 2-point locking

**EAN:** 6418074079220  
**EI. number:**  
 Finland: 3423099  
 Electric No. 8212091090  
 Denmark:  
 Electric No. Sweden: 2500116



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening. Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	500	400	210	MPP ARCA 5040	Mounting plate perforated (450x350x2 mm - 26x11 mm)
inch:	19.7	15.7	8.3	MPMP ARCA 5040	Mounting plate multiperforated (450x350x2 mm - □3.6 mm)
Materials:				MPX ARCA 5040	Mounting plate (450x350 mm)
<b>Material:</b>	Polycarbonate			DRS ARCA 504015	DIN rail frame set
<b>Base colour:</b>	RAL 7035 -light grey			DRS ARCA 504021	DIN rail frame set
<b>Cover colour:</b>	RAL 7035 -light grey			IDS ARCA 5040	Inner door set
<b>Gasket material:</b>	Polyurethane			PMK ARCA 40	Pole mounting kit
				RCS ARCA 5040	Rain canopy set
Temperatures:				Rating:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Ingress Protection (EN 60529): IP66	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Electrical insulation: Totally insulated	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
Accessories:				UV resistance: UL 508	
MPS ARCA 5040	Mounting plate (450x350x2 mm)			Flammability Rating: UL 746C 5V	
				Glow Wire Test (IEC 695-2-1) °C: 960	
Certificates:				SGS Fimko	
				Gost R	

