

**ARCA 504021W**



Sample photo

**Order symbol:** ARCA 504021W  
**Product nbr:** 8120131  
**Description:** Cabinet, PC  
**Remarks:** Cover with window, 2-point locking

**EAN:** 6418074080028  
**EI. number:**  
 Finland: 3423204  
 Electric No. 8212091870  
 Denmark:  
 Electric No. Sweden: 2500144

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening. Door guide included.

Dimensions:	Length	Width	Height	Accessories:
mm:	500	400	210	MPP ARCA 5040
inch:	19.7	15.7	8.3	MPMP ARCA 5040

Materials:	Accessories:
<b>Material:</b> Polycarbonate	Mounting plate perforated (450x350x2 mm - 26x11 mm)
<b>Base colour:</b> RAL 7035 -light grey	MPX ARCA 5040
<b>Cover colour:</b> RAL 7035 -light grey	DRS ARCA 504015
<b>Gasket material:</b> Polyurethane	DRS ARCA 504021
	IDS ARCA 5040
	PMK ARCA 40
	RCS ARCA 5040

Temperatures:	Rating:
<b>Temperature °C (short term):</b> -40 ... 120 °C	Ingress Protection (EN 60529): IP65
<b>Temperature °C (continuous):</b> -40 ... 80 °C	Impact Resistance (EN 62262): IK08
<b>Temperature °F (short term):</b> -40 ... 250 °F	Electrical insulation: Totally insulated
<b>Temperature °F (continuous):</b> -40 ... 175 °F	Halogen free (DIN/VDE 0472, Part 815): 1
	UV resistance: UL 508
	Glow Wire Test (IEC 695-2-1) °C: 960

Accessories:	Certificates:
MPS ARCA 5040	SGS Fimko
Mounting plate (450x350x2 mm)	Gost R

