

EKIV 33

Sample image

Order symbol: EKIV 33

Product nbr: 4712118

Description: Back Panel. for enclosures:

Remarks: 300x300x170. 300x300x180. 600x300x170

EAN: 6418074032720

Including:

El. number:

- Finland: 3424451
- Denmark: 8212014585
- Sweden: 2539352

EKIV_23-64H

Dimensions:	Height	Width	Depth
mm:	270	270	1
inch:	10.63	10.63	0.04

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C: C

NEMA Class

Temperatures:

Temperature °C (short term)::

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Certificates: