






SEMPERCARE® LATEX POWDERED AND VINYL						
Brand Name	Sempercure® latex powdered	Sempermed® latex powdered ASTM	Sempercure® syn-stretch	Sempercure® vinyl powderfree	Sempercure® vinyl powdered	
						
KEY GLOVE FEATURES	1) powdered for easy donning 2) finger textured for good handling of instruments 3) high wearing comfort	1) powdered for easy donning 2) finger textured for good handling of instruments 3) high wearing comfort	1) more elastic than usual Vinyl gloves 2) free of natural rubber latex (suitable for people with type I allergy) 3) free from accelerant chemicals	1) free of natural rubber latex (suitable for people with type I allergy) 2) free from accelerant chemicals (suitable for people with type IV allergy) 3) DOP free		
BASIC INFORMATION						
Reference Number	8239 8102x („x“ = 1 for XS, 3 for S, 5 for M, 7 for L, 9 for XL)	pcs. 8261 52x27 pair 8262 52x27 („x“ = 6 for S, 7 for M, 8 for L)	8239 8022x („x“ = 1 for XS, 3 for S, 5 for M, 7 for L, 9 for XL)	8257 9323x („x“ = 1 for XS, 3 for S, 5 for M, 7 for L, 9 for XL)	100 pcs. 8257 8103x 200 pcs. 8257 9193x („x“ = 1 for XS, 3 for S, 5 for M, 7 for L, 9 for XL)	100 pcs. 8259 8102x 200 pcs. 8259 9182x („x“ = 1 for XS, 3 for S, 5 for M, 7 for L, 9 for XL)
Material	natural latex	natural latex	natural latex	synthetic polymer / vinyl	vinyl	vinyl
Powder-free/powdered sterile/unsterile	powdered unsterile	powdered sterile	powdered unsterile	powder free unsterile	powder free unsterile	powdered unsterile
Length	median 240 mm	median 240 mm	min. 230 mm	median 240 mm	median 240 mm	median 240 mm
Inner	powdered (cornstarch)	powdered (cornstarch)	powdered (cornstarch)	inner coated	inner coated	powdered (cornstarch)
Surface	grippy	grippy	grippy	smooth	smooth	smooth
Typical production values thickness @ palm (double)	median 0.21 mm	median 0.21 mm	median 0.19 mm	median 0.14 mm	median 0.10 mm	median 0.10 mm
FORCE AT BREAK typical production value	median 6 N	median 6 N	not specified	median 3.6 N	median 3.6 N	median 3.6 N
Durability	5 years	5 years	5 years	3 years	5 years	5 years
Color	white	white	white	yellowish	transparent	transparent
Proteins	✓	✓	✓	no	no	no
Accelerating chemicals	✓	✓	✓	no	no	no
LABELLING						
MDD (medical device directive)	CE Class I	CE Class Is	no	CE Class I	CE Class I	CE Class I
PPE (personal protective equipment)	CE Category III complex risk	no	no	CE Category III complex risk	CE Category I minimal risk	CE Category I minimal risk
ASTM	✓	✓	✓	✓	✓	✓
EN 455	✓	✓	no	✓	✓	✓
EN 420	✓	✓	no	✓	✓	✓
EN 374-1, -2	✓	✓	no	✓	✓	✓
EN 374-3	✓	✓	no	✓	no	no
AQL for pinholes (inspection level G1)	1.5	1.5	2.5	1.5	1.5	1.5
Food	✓	✓	no	no	no	no
USAGE RECOMMENDATION						
Hospital	✓	✓	✓	✓	✓	✓
Long Term Care	✓	✓	✓		✓	✓
Medical Practitioners	✓		✓	✓	✓	✓
Dental Sector	✓		✓			
PACKAGING / LOGISTIC INFORMATION						
Available sizes	XS/S/M/L/XL	S/M/L	XS/S/M/L/XL	XS/S/M/L/XL	XS/S/M/L/XL	XS/S/M/L/XL
Pcs / dispenser	XS/S/M/L: 100 pcs. XL: 90 pcs.	pairs: S/M/L: 50 pairs pcs: S/M/L: 50 pcs	XS/S/M/L: 100 pcs. XL: 90 pcs.	XS/S/M/L: 100 pcs. XL: 90 pcs.	XS/S/M/L 100 or 200 pcs. XL: 90 or 180 pcs.	XS/S/M/L 100 or 200 pcs. XL: 90 or 180 pcs.
Pcs / transport carton	XS/S/M/L: 1.000 pcs. XL: 900 pcs.	pairs: S/M/L: 300 pairs pcs: S/M/L 300 pcs	XS/S/M/L: 1.000 pcs. XL: 900 pcs.	XS/S/M/L: 1.000 pcs. XL: 900 pcs.	XS/S/M/L 1.000 or 2.000 pcs. XL: 900 or 1.800 pcs.	XS/S/M/L 1.000 or 2.000 pcs. XL: 900 or 1.800 pcs.