

NSY2SPIHD126

Spacial SFHD outdoor heavy duty - side panel -
inside fixing - H1200 W630



Main

Range	Spacial
Product specific application	Outdoor heavy duty
Accessory / separate part category	Enclosure accessory
Product or component type	Side panel
Device application	Multi-purpose
Enclosure nominal dimensions	1281 mm W: 600 mm 1281 mm W: 800 mm 1281 mm W: 1200 mm
Mounting location	Sides of enclosure
Range compatibility	Spacial SFHD
Device composition	2 side panel Fixing elements

Complementary

Quantity per set	Set of 1
Material	Steel with anti-corrosive coating
Colour	Grey RAL 7035
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - screw type captive - from the inside of enclosure location
Height	Nominal : 1281 mm
Width	Nominal : 630 mm
Depth	Real : 60 mm

Environment

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.