

## NSYS3X4320

SPACIAL S3X stainless 304L, Scotch Brite® finish, H400xW300xD200 mm.



### Main

Range	Spacial
Product name	Spacial S3X
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	400 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	200 mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 door 1 lock ( door )

### Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face : 1 door(s)
Door opening side	120 °, reversible
Lock type	3 mm double-bar lock
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door fixing: by hinges
Material	Lock : zamak Hinge : stainless steel Body and door : stainless steel 304L
Surface finish	Lock : chromium plated Body and door : Scotch-Brite® brushed
Thickness	1.5 mm

### Environment

standards	IEC 62208
product certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
environmental characteristic	Corrosive Specific hygiene

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period

18 months