

NSYSDF108

Spacial SD Control desk with console -
H1400xW1000xD845 - IP55



Main

Range	Spacial
Product name	Spacial SD
Device application	Multi-purpose
Product or component type	Control desk with console and desk
Enclosure nominal height	1400 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	845 mm
Installation accessory type	Floor-standing
Device composition	Cable gland plate 1 Structure 1 Adjustment rail 4 Pneumatic stay 2 desk lid Front console door 1 Desk lid 1 Mechanical stay 2 front console door Lock 6 front door Handle lock 1 rear door Front door 2 Rear door 2

Complementary

Body type	Single piece structure folded and welded
Door type	Plain
Number of doors	2 front 2 rear
Door opening side	Reversible 120 ° front and rear doors Folding 75 ° desk lid and console cover
Lock type	2 points lock, 3 mm double-bar Handle lock, 5 mm double bar
Mounting plate description	Without mounting plate
Type of gland plate	1 entry plate
Accessibility for operation	Front Rear
Removable parts	Desk lid by hinges Cable gland plate by clipping screws Front door by hinges Front console door by hinges Rear door by hinges
Material	Steel body
Surface finish	Epoxy-polyester powder
Thickness	1.5 mm

Environment

standards	IEC 62208
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------