



Main

Range	Spacial
Product name	Spacial SF
Device application	Multi-purpose
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	1000 mm
Enclosure nominal depth	400 mm
Enclosure mounting	Floor-standing
Device composition	1 door 1 rear panel 1 roof 1 structure 1 locking system with handle for door 2 sliding rails 4 mounting plate bracket

Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Door type	Glazed on front
Number of doors	1 on front
Door opening side	Reversible 120 °
Lock type	4 points lock, handle with 5 mm double bar insert on front door
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front Rear Sides of enclosure
Removable parts	Rear panel fixed by screws Roof fixed by screws Door fixed by screws for hinge Mounting plate bracket fixed by screws Sliding rail fixed by screws
Material	Galvanised steel for frame Galvanised steel for uprights Polyamide 6 with 30 % fibre glass for handle Securit glass for door Sheet steel for door Sheet steel for panels Zamak for hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure : grey RAL 7035 Handle : black RAL 9005

Environment

standards	IEC 62208
product certifications	BV DNV UL
IP degree of protection	IP55 conforming to IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------