

NSYSFX20840

SFX 304L stainless suitable enclosure,
H2000xW800xD400mm, Scotch Brite® finish.



Main

Range	Spacial
Product name	Spacial SFX
Device application	Multi-purpose
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	800 mm
Enclosure nominal depth	400 mm
Installation accessory type	Floor-standing
Device composition	1 cable gland plate 1 structure 4 mounting plate bracket 1 locking system with handle (door) 1 door with reinforcement frame

Complementary

Body type	Rear panel integrated Single piece structure folded and welded
Door type	Plain
Number of doors	Front face : 1 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front Side
Removable parts	Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips
Material	Hinge : stainless steel Structure and door : stainless steel 304L Handle : zamak
Surface finish	Enclosure : Scotch-Brite® brushed Handle : painted

Environment

standards	IEC 62208
product certifications	UL
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
environmental characteristic	Corrosive Specific hygiene

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------
