



## Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Device application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 1 cable gland plate 1 door 1 locking system with handle for door 4 mounting plate bracket
Removable parts	Door fixed by screws for hinge Mounting plate bracket fixed by screws
Enclosure nominal height	2000 mm
Enclosure nominal width	800 mm
Enclosure nominal depth	600 mm

## Complementary

Number of doors	1 on front
Door opening side	Reversible 120 °
Door type	Glazed
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry
Material	Securit glass for door Sheet steel for body Sheet steel for door Zamak for hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure : grey RAL 7035 Handle : black RAL 9005
Accessibility for operation	Front

## Environment

standards	IEC 62208
product certifications	BV DNV UL
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Product end of life instructions

Need no specific recycling operations

---

### Contractual warranty

Warranty period

18 months

---