

NSYSMHF20860P

Spacial SM EMC compact enclosure without mounting plate - H2000xW800xD600mm



Main

Range	Spacial
Product name	Spacial SMHF
Product or component type	Compact enclosure
Device application	Multi-purpose
Installation accessory type	Floor-standing
Enclosure nominal height	2000 mm
Enclosure nominal width	800 mm
Enclosure nominal depth	600 mm

Complementary

Number of doors	1 on front
Door opening side	Right or left 120 °
Door type	Plain
Lock type	5 mm double bar head
Mounting plate description	Without mounting plate
Type of gland plate	1 gland plate
Cable entry	1 entry
Material	Aluzinc for body Aluzinc for door
Surface finish	Epoxy-polyester powder
Colour	Enclosure : grey RAL 7035 Handle : black RAL 9005
Accessibility for operation	Front

Environment

standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.