

# NSYSMX181640H

SMX 316L stainless monobloc enclosure,  
H1800xW1600xD400mm, Scotch Brite® finish.



## Main

Range	Spacial
Product name	Spacial SMX
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	1800 mm
Enclosure nominal width	1600 mm
Enclosure nominal depth	400 mm
Installation accessory type	Floor-standing
Device composition	1 body 1 cable gland plate 4 mounting plate bracket 2 door 1 locking system with handle ( door )

## Complementary

Body type	Single piece body folded and welded
Door type	Plain
Number of doors	Front face: 2 door(s)
Door opening side	120 °, reversible
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front
Removable parts	Door fixing: by hinges Mounting plate bracket fixing: by screws Cable gland plate fixing: by clips
Material	Handle: zamak Hinge: stainless steel Body and door: stainless steel 316L
Surface finish	Enclosure: Scotch-Brite® brushed Handle: painted
Thickness	1.5 mm

## Environment

standards	IEC 62208
product certifications	UL 508 CAN/CSA 22
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
environmental characteristic	Corrosive Specific hygiene

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---