

NSYSMX18660PC

Stainless 304L PC rack, Micro-beading finishing,
H1800xW600xD600mm.



Main

Range	Spacial
Product name	Spacial SMX
Device application	PC application Computer protection
Product or component type	Compact enclosure
Enclosure nominal height	1800 mm
Enclosure nominal width	600 mm
Enclosure nominal depth	600 mm
Installation accessory type	Floor-standing
Device composition	1 body 1 cable gland plate 1 partial door for keyboard 1 partial door for PC screen 1 rear door 1 partial door for printer support/CPU

Complementary

Body type	Single piece body folded and welded
Door type	Plain Plain partial Glazed partial
Number of doors	Front: 2 door(s) Front : 1 door(s) Rear : 1 door(s)
Door opening side	120 °, reversible
Lock type	3 mm double-bar lock
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front Rear
Removable parts	Cable gland plate fixing: by clips Rear: door fixing: by hinges Front: partial doors fixing: by hinges Transparent shutter fixing: by screws
Material	Body and door: stainless steel 304L Hinge: stainless steel Door: Securit glass Lock: zamak
Surface finish	Body and door: micro beaded Securit glass: silkscreened Lock: chromium plated

Environment

standards	IEC 62208
IP degree of protection	IP55 (even with the keyboard drawer open) conforming to IEC 60529
IK degree of protection	IK10 (plain door) conforming to IEC 62262 IK08 (glazed door) conforming to IEC 62262
environmental characteristic	Corrosive Specific hygiene

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold
-------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
