

Datasheet

Item no. 1583036

V1_0624_01_de

Rohrkabelschuhe

Material : Kupfer
Norm : Handelsüblich, ähnlich DIN 46235

Auf Anfrage: 185 mm², 240 mm² und 300 mm²



Artikel- bezeichnung	Querschnitt mm ²	AWG	Lochdurchmesser (mm)	X (mm)	D (mm)	a (mm)	l (mm)	b (mm)	VPE
PKK 60.05	6,0	10	5,0	3,6	5,6	9,0	21,0	11,5	100
PKK 60.06	6,0	10	6,0	3,6	5,6	9,0	21,0	11,5	100
PKK 60.08	6,0	10	8,0	3,6	5,6	9,0	23,0	13,0	100
PKK 60.10	6,0	10	10,0	3,6	5,6	9,0	25,0	16,0	100
PKK 60.12	6,0	10	12,0	3,6	5,6	9,0	25,0	19,0	100
PKK 100.05	10,0	8	5,0	4,5	7,0	10,0	21,0	12,0	100
PKK 100.06	10,0	8	6,0	4,5	7,0	10,0	21,5	12,0	100
PKK 100.08	10,0	8	8,0	4,5	7,0	10,0	23,5	15,0	100
PKK 100.10	10,0	8	10,0	4,5	7,0	10,0	25,5	17,0	100
PKK 160.05	16,0	6	5,0	5,5	8,5	13,0	25,0	12,0	100
PKK 160.06	16,0	6	6,0	5,5	8,5	13,0	25,5	12,0	100
PKK 160.08	16,0	6	8,0	5,5	8,5	13,0	27,5	15,0	100
PKK 160.10	16,0	6	10,0	5,5	8,5	13,0	29,5	17,0	100
PKK 160.12	16,0	6	12,0	5,5	8,5	13,0	30,5	19,0	100
PKK 250.05	25,0	4	5,0	7,2	10,0	15,0	28,0	14,0	100
PKK 250.06	25,0	4	6,0	7,2	10,0	15,0	28,5	14,0	100
PKK 250.08	25,0	4	8,0	7,2	10,0	15,0	30,5	16,0	100
PKK 250.10	25,0	4	10,0	7,2	10,0	15,0	32,5	18,0	100
PKK 250.12	25,0	4	12,0	7,2	10,0	15,0	33,5	19,0	100
PKK 350.06	35,0	2	6,0	8,5	12,0	17,0	31,5	18,0	100
PKK 350.08	35,0	2	8,0	8,5	12,0	17,0	33,5	18,0	100
PKK 350.10	35,0	2	10,0	8,5	12,0	17,0	35,5	18,0	100
PKK 350.12	35,0	2	12,0	8,5	12,0	17,0	36,5	20,0	100

Datasheet

Item no. 1583036

V1_0624_02_de

Artikel- bezeichnung	Querschnitt mm ²	AWG	Lochdurchmesser (mm)	X (mm)	D (mm)	a (mm)	l (mm)	b (mm)	VPE
PKK 500.06	50,0	1/0	6,0	10,2	14,0	19,0	34,5	20,0	100
PKK 500.08	50,0	1/0	8,0	10,2	14,0	19,0	36,5	20,0	100
PKK 500.10	50,0	1/0	10,0	10,2	14,0	19,0	38,5	20,0	100
PKK 500.12	50,0	1/0	12,0	10,2	14,0	19,0	39,5	23,0	100
PKK 500.16	50,0	1/0	16,0	10,2	14,0	19,0	42,5	28,0	100
PKK 700.06	70,0	2/0	6,0	12,0	16,5	21,0	40,5	23,0	50
PKK 700.08	70,0	2/0	8,0	12,0	16,5	21,0	40,5	23,0	50
PKK 700.10	70,0	2/0	10,0	12,0	16,5	21,0	43,5	23,0	50
PKK 700.12	70,0	2/0	12,0	12,0	16,5	21,0	43,5	23,0	50
PKK 700.14	70,0	2/0	14,0	12,0	16,5	21,0	46,5	28,0	50
PKK 700.16	70,0	2/0	16,0	12,0	16,5	21,0	46,5	28,0	50
PKK 950.08	95,0	3/0	8,0	13,5	17,8	24,0	47,0	25,0	50
PKK 950.10	95,0	3/0	10,0	13,5	17,8	24,0	47,0	25,0	50
PKK 950.12	95,0	3/0	12,0	13,5	17,8	24,0	47,0	25,0	50
PKK 950.14	95,0	3/0	14,0	13,5	17,8	24,0	50,0	25,0	50
PKK 950.16	95,0	3/0	16,0	13,5	17,8	24,0	50,0	29,0	50
PKK 1200.08	120,0	4/0	8,0	15,0	19,5	26,0	50,0	29,0	30
PKK 1200.10	120,0	4/0	10,0	15,0	19,5	26,0	50,0	29,0	30
PKK 1200.12	120,0	4/0	12,0	15,0	19,5	26,0	50,0	29,0	30
PKK 1200.14	120,0	4/0	14,0	15,0	19,5	26,0	53,0	29,0	30
PKK 1200.16	120,0	4/0	16,0	15,0	19,5	26,0	53,0	29,0	30
PKK 1200.20	120,0	4/0	20,0	15,0	19,5	26,0	57,5	35,0	30
PKK 1500.10	150,0	5/0	10,0	16,5	20,8	29,0	54,0	31,0	10
PKK 1500.12	150,0	5/0	12,0	16,5	20,8	29,0	54,0	31,0	10
PKK 1500.16	150,0	5/0	16,0	16,5	20,8	29,0	57,0	31,0	10
PKK 1500.20	150,0	5/0	20,0	16,5	20,8	29,0	61,5	35,0	10