

M4 Stud Size 30A Blue Ring Connector Pack of 100

Order code: **33-0910**

Note:

- 1. Maximum electric current:
- 2. Maximum electrical rating:
- 3. Insulation material:
- 4. Insulator colour:
- 5. Terminal material:
- 6. Wire range:
- 7. Terminal surface treatment:
- 8. Terminal thickness:

AWG	16	14
AMP	18	30

105°C 600 volts max.

Vinyl

Blue

Copper

16-14 AWG (1.5-2.5mm²)

Tin plated

0.80mm

