

M5 Stud Size 48A Yellow Ring Connector Pack of 100

Order code: **33-1210**

Note:

1. Maximum electric current:
2. Maximum electrical rating:
3. Insulation material:
4. Insulator colour:
5. Terminal material:
6. Wire range:
7. Terminal surface treatment:
8. Terminal thickness:

AWG	12	10
AMP	3	50

105°C 600 volts max.

Vinyl

Yellow

Copper

12-10 AWG (4-6mm²)

Tin plated

1.0mm

