

## Countersunk Head Pozidriv<sup>®</sup> Machine Screws - Packs of 100



### DESCRIPTION

Countersunk Head Pozidriv<sup>®</sup> Machine Screws with bright zinc-plated, passivated finish.

### DISTINCTIVE FEATURES

- Pozidriv<sup>®</sup>
- Steel Grade 4.8
- M3, M4 and M5 options
- Zinc & Clear Cr3 Finish
- Flat, Countersunk head style
- Supplied in packs of 100

### APPLICATIONS

Designed for use where a flush surface finish is required. Suitable for general use. Typical applications include use in electrical, electronic and domestic equipment, general repair and maintenance, circuit board mounting, prototyping, etc.

Countersunk  
Head

Grade  
4.8  
Steel

Zinc  
& Clear  
Cr3





## GENERAL SPECIFICATION

Series	Machine Screws
Type	PoziDriv®



## MATERIALS

Material	Grade 4.8 Steel
Finish	Zinc & Clear Cr3



## CERTIFICATION AND STANDARDS

Material Specification	DIN 965Z ~ISO 7046
------------------------	--------------------





## OPTIONS (MOQ may apply)

Lengths	Various
Thread Sizes	M1.6 to M12
Thread Type	Coarse and Fine
Material	Steel
Head Styles	e.g. Button, Pan, Cheese



## DIMENSIONS/DRAWINGS

Units	mm - unless stated otherwise
-------	------------------------------





## PART NUMBER TABLE

Part number	A Thread size	B Length	C Screwdriver size	D Head width	E Head depth	F Screwdriver depth	UNSPSC	EAN	Country of Origin
<b>33-7067</b>	M3	6	PZ1 - 2.9	5.6	1.65	1.48-1.73	73181900	5053556009800	China
<b>33-7068</b>		10					73181900	5053556009817	China
<b>33-7069</b>		12					73181900	5053556009824	China
<b>33-7070</b>		16					73181900	5053556009831	China
<b>33-7071</b>		20					73181900	5053556009848	China
<b>33-7072</b>		25					73181900	5053556009855	China
<b>33-7073</b>	M4	6	PZ2 - 4.40	7.5	2.20	1.6-2.06	73181900	5053556009862	China
<b>33-7074</b>		10					73181900	5053556009879	China
<b>33-7075</b>		12					73181900	5053556009886	China
<b>33-7076</b>		16					73181900	5053556009893	China
<b>33-7077</b>		20					73181900	5053556009909	China
<b>33-7078</b>		25					73181900	5053556009916	China
<b>33-7079</b>	M5	10	PZ2 - 4.60	9.20	2.5	2.05-2.51	73181900	5053556009923	China
<b>33-7080</b>		12					73181900	5053556009930	China
<b>33-7081</b>		16					73181900	5053556009947	China
<b>33-7082</b>		20					73181900	5053556009954	China
<b>33-7083</b>		25					73181900	5053556009961	China

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



**Important Notice:** This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.