

Pan Head Pozidriv[®] Machine Screw - Packs of 100



DESCRIPTION

Pan Head Pozidriv[®] Stainless Steel Machine Screws with good corrosion resistance. Suitable for outdoor use.

DISTINCTIVE FEATURES

- Pozidriv[®]
- Self-coloured Finish
- Stainless Steel Grade A2 (304)
- Corrosion Resistant
- Non-magnetic
- Dome head style
- M2.5, M3 and M4 options
- Supplied in packs of 100

APPLICATIONS

Applications include electronic and domestic equipment, and general maintenance and construction use. Suitable for outdoor use and where improved corrosion resistance is required. Suitable for use in food, medical and non-severe chemical environments, and in both low and high temperature applications.

Note: Not suitable for use with non-oxidising acids and agents or in chloride rich environments.

**Pan
Head**

**Stainless
Steel**

**Self
Colour**





GENERAL SPECIFICATION

Series	Machine Screw
Type	PoziDriv®



MATERIALS

Material	A2 Stainless Steel
Finish	Self Colour



CERTIFICATION AND STANDARDS

Material Specification	DIN 7985Z ~ISO 7045
------------------------	---------------------





OPTIONS (MOQ may apply)

Lengths	Various
Thread Sizes	M1.6 to M12
Thread Type	Coarse and Fine
Material	Steel
Head Styles	e.g. Button, Countersunk, Cheese



DIMENSIONS/DRAWINGS

Units	mm - unless stated otherwise
-------	------------------------------



PART NUMBER TABLE

Part number	A Thread size	B Length	C Screwdriver size	D Head width	E Head depth	F Screwdriver depth	UNSPSC	EAN	Country of Origin
33-7087	M2.5	6.0	PZ1 - 2.6	5.0	2.12	1.27-1.52	73181900	5053556010004	China
33-7088		12.0					73181900	5053556010011	China
33-7089	M3	6.0	PZ1 - 3.0	6.0	2.52	1.68-1.93	73181900	5053556010028	China
33-7090		12.0					73181900	5053556010035	China
33-7091		20.0					73181900	5053556010042	China
33-7092	M4	6.0	PZ2 - 4.3	8.0	3.25	1.9-2.36	73181900	5053556010059	China
33-7093		12.0					73181900	5053556010066	China

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.