

| Order code | Manufacturer code | Description |
|-------------------|--------------------------|--------------------------|
| 35-0040 | n/a | 6V LOW PROFILE BUZZER RC |

| | |
|--|--------------------------|
| | Page 1 of 2 |
| The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E. | Revision A 20/02/2007 |

SPECIFICATION

1. Rated Voltage 5VDC
2. Operating Voltage 3~8VDC
3. Max. Rated Current 30mA/5VDC
4. Min. Sound Pressure Level 85dB/10cm
5. Resonant Frequency 3100±500Hz
6. Response Time 50ms
6. Case Material PBT
7. Operating Temperature -20~+85°C
8. Store Temperature -20~+88°C
9. Weight 2g

