

Order code	Manufacturer code	Description
35-0262	n/a	12V PCB PIEZO INDICATOR 3-20VDC (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

ABI-003-RC SPECIFICATION SHEET

Features:

- High Sound Output
- Sealed Base

All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABI-003-RC – Piezo Indicator
Rated Voltage	12VDC
Operating Voltage	3 ~ 20VDC
Rated Current at rated voltage	15mA
Min Sound Output at 10cm, at rated voltage	95dB
Resonant Frequency	3400±500Hz
Tone	Continuous
Operating Temperature	-20 ~ +60°C
Storage Temperature	-30 ~ +70°C
Weight	4g

Value applying rated voltage (DC)

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

