

DATA SHEET

Order code	Manufacturer code	Description
35-0270	n/a	6V PCB ELECTRO MECH INDICATOR (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to	Revision A
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	04/07/2003

Sales: 01206 751166 Technical: 01206 835555 Fax: 01206 7551188 Sales@rapidelec.co.uk Tech@rapidelec.co.uk www.rapidelectronics.co.uk

ABI-009-RC SPECIFICATION SHEET

Features:

• Colour: Black

Housing Material: NorylBuilt in oscillating circuit

• Wave solderable and washable

All data at 25°C unless otherwise specified.

SPECIFICATIONS	ABI-009-RC	
	Electro-mechancial Indicator	
Rated Voltage	6VDC	
Operating Voltage	4~8VDC	
Rated Current at rated voltage	30mA	
Sound Output at 10cm, at rated voltage	≥85dB	
Resonant Frequency at rated voltage	2300 ± 300 Hz	
Operating Temperature	-20 ~ +70°C	
Storage Temperature	-30 ~ +80°C	
Weight	2g	

DIMENSIONS: (UNIT: mm, TOLERANCE: ±0.5mm)

