

DATA SHEET

Loudspeakers

	Order code	Manufacturer code	Description
Г	35-1400	n/a	75MM FULL RANGE LOUDSPEAKER

Loudspeakers	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to	Revision A
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	04/07/2003

Sales: 01206 751166 Technical: 01206 835555 Fax: 01206 7551188 Sales@rapidelec.co.uk Tech@rapidelec.co.uk www.rapidelectronics.co.uk

PA & Audio / Video

Technical Specifications:

Loudspeaker Type: Woofer (340M)

Nominal Impedance: 8 Ohm Resonant Frequency: 120Hz

Usable Frequency Response: 120Hz – 16kHz

Nominal Power Handling: 10W Music Power Handling: 20W

Sensitivity (SPL): 88dB/W/0.5m

Chassis Shape: Round
Chassis Diameter: 78mm
Magnet Housing Diameter: 70mm
Driver Depth: 40mm
Cone Diameter: 62mm

Fixing Centers: 4 x 3.5mm Ø holes at 90° intervals on a 84mm Ø Circle

Baffle Cut Out: $78 \text{mm } \emptyset$ Overall Weight: 400 g

Physical Dimensions:

