

Order code	Manufacturer code	Description
35-6116	n/a	192-CHANNEL DMX CONT. W/ JOYSTICK (RC)

	Page 1 of 3
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007



Choose your language: English (UK)



Search Product:

[[Advanced](#)]

[SOUND & LIGHT PRODUCTS](#) > [PROFESSIONAL LIGHTING CONTROLS - HQ-POWER](#) >



192-CHANNEL DMX CONTROLLER WITH JOYSTICK

Order Code: VDPC174



Features

- 192 DMX channels
- 12 scanners of 16 channels each
- 30 banks of 8 programmable scenes
- 6 programmable chases of 240 scenes
- 8 sliders for manual control of channels
- assignable joystick for ease of use with pan & tilt channels
- file dump allows the transfer of data between two units
- programmable auto mode controlled by speed and fade time sliders
- assignable fade time
- invertible DMX channels make it possible to have a device execute the normal sequence backwards
- 8-channel or 16-channel mode
- fine adjustment for joystick pan and tilt
- master blackout button
- manual override button allows the user to pilot an arbitrary device manually
- built-in microphone for music triggering
- MIDI control for MIDI-triggered operation
- polarity selector for DMX connector
- backup memory

[More...](#)



Specifications

- [19" rack hardware](#)
- [Audio appliances](#)
- [Blacklight armatures](#)
- [Blacklights + holder](#)
- [Blinders](#)
- [Decorative lighting & party lights](#)
- [Disco accessories](#)
- [Disco light kits](#)
- [Disco lights](#)
- [Dispatching](#)
- [Dual cone speaker sets](#)
- [Fluorescent tubes](#)
- [Headphones](#)
- [Instrument stands](#)
- [Laser products](#)
- [Led disco lights](#)
- [Led tubes](#)
- [Lighting stands](#)
- [Loudspeaker cables](#)
- [Loudspeakers - eminence](#)
- [Microphones](#)
- [Mini box systems](#)
- [Mirror balls](#)
- [Neutrik](#)
- [Pa systems](#)
- [Par spots](#)
- [Piezo hi-fi tweeters](#)
- [Professional cables](#)
- [Professional lighting controls - hq-power](#)
- [Professional lighting controls - lite-puter](#)
- [Professional sound equipment omnitronic](#)
- [Promo packs](#)
- [Public address systems](#)
- [Rotating lights](#)
- [Smoke machines & effects](#)
- [Speaker accessories](#)
- [Speakers](#)
- [Spot accessories](#)
- [Stroboscopes](#)



[Velleman Brochure](#)

- power supply: 9-12VDC, 500mA
- DMX in/out: 3-pin female/male XLR socket
- MIDI in: 5-pin DIN socket
- dimensions: 19" x 134mm (2U) x 85mm
- weight: 2.7kg

Stock Info

- Inner carton:
- Outer Carton: 4
- EAN Barcode: 5410329368920
- Packaging: Box (Carton)

Please check www.vellemanusa.com for availability in the USA and Canada.

(C) 2008 Velleman Components N.V.
[[Disclaimer](#)]