




AmpFlow A28-150-G, 8.26:1, 24V



REVISIONS				
ECO	REV	DESCRIPTION	DATE	APPROVED



NOMINAL VOLTAGE: 24
NO-LOAD RPM: 720



DO NOT SCALE THIS DRAWING		POLYMERES UNLESS OTHERWISE NOTED		SIGNATURE	DATE	Powerhouse Engineering
		2 PLG	3 PLG	ANGLE	DETAIL	
MATERIAL		±		±	±	A28-150-G
		REMOVE ROUNDS & SHARP EDGES		APP'D		
FINISH		SURFACE FINISH		THIRD ANGLE PROJECTION		SIZE C DRAWING NUMBER SCALE 1.000
		DIMENSIONS ARE IN INCHES				
						REV
						SHEET 1 OF 1