

## BATTERY OPERATED (BO) SERIES

### BO-7 (OUTPUT BY BOTH SIDE)

**Gear Ratio:**  
(1:120, 1:200)

**Operating Voltage:**  
3.0~12.0V DC  
**Without Loading:**  
40~230mA  
25~100rpm

**Output Torque:**  
2~12Kgf.cm  
**Weight:**  
31.9g

