



Main

Range	ClimaSys
Product name	ClimaSys CC
Product or component type	Electronic hygrotherm
Temperature setting range	-40...80 °C
Humidity setting range	20...80 %
Display type	OLED screen
Information displayed	Relative humidity Temperature in °C Temperature in °F

Complementary

Input voltage	90...140 V AC
Sensor type	Optional NTC external sensor
Maximum switching capacity	4 A 120 V AC
Electrical connection	8 connectors 2.5 mm ²
Mounting mode	By screws Clipped
Height	External : 85 mm
Width	External : 56 mm
Depth	External : 44 mm
Mounting location	On mounting plate 35 mm DIN rail Spacial upright Cross rails
Ambient air temperature for operation	-40...80 °C
Hysteresis	2 K programmed value
Hysteresis	3 %
Number of outputs	2 output(s) ventilation/heating function
Material	PC
Colour	Light grey
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product certifications	UR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------