

NSYCR150WU1C

ClimaSys PTC heating resistance 150W, 12-24V
insulate



Main

Range	ClimaSys
Product name	ClimaSys CR
Product or component type	Resistance heater
Power range	150 W
Input voltage	12...24 V DC
Electrical connection	4 screw terminals 2.5 mm ²

Complementary

Operating position	Vertical
Ambient air temperature for operation	-40...70 °C
IP degree of protection	IP20
Electrical insulation class	Class II
Product certifications	UL VDE
Material	Extruded aluminium for body Plastic for cover
Height	External: 150 mm
Width	External: 60 mm
Depth	External: 90 mm
Condition of use	Electrical protection is needed Heaters must be installed with a thermal controller Air sealed enclosure
Fixing mode	By clips
Mounting support	35 mm DIN rail

Environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.