


MEG 20mm CARBON ROTARY **POTENTIOMETERS**

SINGLE SWITCHED 1 AMP

PC 20 BU/PC IS



OW 20 BU/OW IS

As PC 20 BU/PC IS except ordinary wiring tags

SPINDLE VARIATIONS

Plastic

Fixed or Plug in





© (₩ ♥	
BUSH VARIA	ATIONS	3
Y(mm)	W(mm)* Type
M10×0.75	7	C or CP
	9	C or CEBS
9.52×32TPi	7	CBS or CBSL
	9	CBS
	40	CDC

CBS M10×0.75 Fixed C or CP M7×0.75 C or CE Fixed 6.35 9.52×32TPi CBS or CBSL CBS or CBSL 12 CBS or CBSL

See also Spindle Data Pages See also Bush Data Pages *+0.5

PC 20 SP/PC IS








Viewed on Component side

SPINDLE VARIATIONS		
Plastic	X(mm)	
Fixed or Plug in	6	
Fixed	4	
Fixed	6.35	
See also Spindle	Data Pages	

TO ORDER Please photocopy the relevant illustration and detail your own requirements. Please confirm that your order has all the information required by the checklist on the first page of this section.



SPINDLE TYPE CODE _____

TRACK VALUE AND LAW _