

PTM111		
Product		Thermostat
Feature		Single
Contact		1NO
Color		Blue
Current	**Ie**	10 A (230V AC)
Usage Category		AC15
Mechanical Life	**Min Qty**	50000
Electrical Life	**Min Qty**	50000
Operating Frequency	**On-Off/Hour**	Mech. 900 Elec. 900
Insulation Voltage	**Ui**	300V
Impulse Withstand Voltage	**Uimp**	2.5 kV
Dielectric Strength (Body-Contact)		2.500V AC
Dielectric Strength (Contact-Contact)		1.500V AC
Isolation Resistance		10 MΩ min. (500V DC)
Operating Temperature		-25 / +80 °C
Pollution Degree		3
Protection Degree		IP20
Contact Material		AgNi
Cable Section		1-2.5 mm²
Screw Torque		1,5 Nm
Short Circuit Breaking Capacity	**Ics**	1 kA
Serial		PTM Series
Specifications	Sensitive setting	
	Plastic housing, DIN rail mountable	
Standards / Certificates	TS EN 60730-2-9	

CE